Rittal – The System.

Faster – better – everywhere.





SV 9342.210 Connection Adapters

State: 2025-11-09 (Source: rittal.com/ca-en)



SV 9342.210 - Connection Adapters

For busbar systems with 60 mm center-to-center distance.

Features

Model No.	SV 9342.210
Material	Cover: ABS Punched section: Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated current max.	63 A
Rated operating voltage	690 V, 3~
Electrical UL ratings (SCCR)	65 kA - 600 V, fuse class J max. 60 A, JDDZ/7 65 kA - 480 V, manual motor controller max. 65 A, NLRV/7
Cable outlet	Bottom
For bar systems with center-to- center spacing	60 mm
Note	The technical data may vary for UL applications. UL approval only applies in conjunction with AC application The rated operating voltage for DC applications depends on the busbar arrangement in the busbar support 9340.050/9341.050/9342.050.
Number of poles	3-pole
Dimensions	Width: 20 mm Height: 215 mm
Connection of round conductors, fine wire with wire end ferrule	2.5 - 10 mm²
Connection of round conductors, single-wire	2.5 - 10 mm²
Connection of round conductors, multi-wire	2.5 - 10 mm²

© Rittal 2025

Features

Connection of round conductors, fine wire without sleeve AWG	2.5 - 10 mm²
Suitable for busbars	Height: 5, 10 mm
Rated operating voltage (L1 + L2)	1000 V (DC)
Rated operating voltage (L1 + L3)	1500 V (DC)
Packaging unit	1 pc(s).
Net weight	0.205
Gross weight	0.206
Copper weight (kg per piece)	0.019
Customs tariff number	85369010
EAN	4028177503601
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3