

# Rittal – The System.

Faster – better – everywhere.



## SV 9342.314

## Connection adapter expansion set

State: 2025-09-07 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9342.314 - Connection adapter expansion set for 4-pole configuration

1-pole extra set to complement the 3-pole connection adaptor (SV 9342.310/9342.320) for 4-pole configurations.

## Features

Model No.	SV 9342.314
Product description	1-pole extra set to complement the 3-pole connection adaptor for 4-pole configurations.
Material	Cover: ABS Punched section: Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated current max.	800 A
Rated operating voltage	690 V, 1~
Electrical UL ratings (SCCR)	65 kA - 480 V, circuit breaker max. 600 A, DIVQ/7 65 kA - 600 V, fuse class L max. 800 A, JDDZ/7
For bar systems with center-to-center spacing	60 mm
Note	The technical data may vary for UL applications. UL approval only applies in conjunction with AC application
Number of poles	1-pole
Suitable for Model No.	9342.310
Dimensions	Width: 50 mm Height: 270 mm
Connection of round conductors, fine wire with wire end ferrule	95 - 185 mm <sup>2</sup>
Connection of round conductors, multi-wire	95 - 300 mm <sup>2</sup>
Suitable for busbars	Height: 5, 10 mm

## Features

Clamping area for laminated copper bars for 5 mm bar thickness, (W x H)	33 x 26 mm
Clamping area for laminated copper bars (W x H)	33 x 21 mm
Clamping area for laminated copper bars for 10 mm bar thickness, (W x H)	33 x 21 mm
Packaging unit	1 pc(s).
Net weight	0.8
Gross weight	0.88
Copper weight (kg per piece)	0.096
Customs tariff number	85369010
EAN	4028177536869
ETIM 9	EC001531
ECLASS 8.0	27370304

## Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK