Rittal – The System.

Faster – better – everywhere.






AX 9204.100 Ex Enclosures

State: 2025-11-04 (Source: rittal.com/ca-en)



AX 9204.100 - Ex Enclosures Fiberglass Reinforced Polyester AX, empty enclosure with hinged door

Ex enclosure with hinged door, fiberglass-reinforced polyester







Features

Model No.	AX 9204.100
Version	Ex Enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EU
	Ambient temperature range: -40 °C+70 °C
	The specified temperatures can be limited by the installed equipment
	Explosion protection category to EN 60 079: Equipment protection
	due to increased safety (Ex e), equipment protection due to
	enclosure (Ex tb)
Material	Housing: fiber-glass reinforced unsaturated polyester, surface
	resistance: < 10 \(Ω \)
	Door: glass fiber reinforced unsaturated polyester, surface
	resistance: < 10 M Ω circumferentially bonded silicone gasket
	Mounting plate: Carbon steel, zinc-plated
Color	RAL 9011
Supply includes	Housing
	Door
	Mounting panel

© Rittal 2025

Features

Dimensions	Width: 400 mm Height: 400 mm Depth: 200 mm
Dimensions of mounting plate (W x H)	305 mm x 325 mm
Material thickness – mounting plate	2.5 mm
Certificate IEC EX PTB 10.0011U	Yes
Certificate PTB 03 ATEX 1011U	Yes
Lock	No. of locks: 2
Protection category IP to IEC 60 529	IP 65
Protection category NEMA	Type 1 Type 3R Type 3RX Type 4 Type 4X Type 12
IK code	IK09
Operating temperature range	-40 °C70 °C
Operating temperature	The specified temperatures can be limited by the installed equipment
Packaging unit	1 pc(s).
Net weight	8.7
Gross weight	8.9
Customs tariff number	94037000
EAN	4028177952089
ETIM 9	EC002503
ECLASS 8.0	27180502

© Rittal 2025 3

Approvals

Approvals	ATEX
	ATEX QA
	IECEx
	IECEx QAR
	UR + C-UR (recognized)
Explanations	Attestation of Conformity

© Rittal 2025