Rittal – The System.

Faster – better – everywhere.





Connection adapter expansion set

State: 2025-10-31 (Source: rittal.com/ca-en)



SV 9342.324 - Connection adapter expansion set for 4-pole configuration

1-pole extra set to complement the 3-pole connection adaptor (SV 9342.310/9342.320) for 4-pole configurations.

Features

| Model No. | SV 9342.324 |
|---|--|
| Product description | 1-pole extra set to complement the 3-pole connection adaptor for 4-pole configurations. |
| Material | Cover: ABS Punched section: Polyamide Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| Rated current max. | 1,600 A |
| Rated operating voltage | 690 V, 1~ |
| Electrical UL ratings (SCCR) | 65 kA - 480 V, circuit breaker max. 1200 A, DIVQ/7 65 kA - 600 V, fuse class L max. 1600 A, JDDZ/7 |
| For bar systems with center-to- center spacing | 60 mm |
| Note | The technical data may vary for UL applications. UL approval only applies in conjunction with AC application |
| Number of poles | 1-pole |
| Suitable for Model No. | 9342.320 |
| Dimensions | Width: 85 mm Height: 270 mm |
| Suitable for busbars | Height: 5, 10 mm |
| Clamping area for laminated copper bars for 5 mm bar thickness, (W x H) | 65 x 27 mm |
| | |

© Rittal 2025

Features

| Clamping area for laminated copper bars (W x H) | 65 x 22 mm |
|--|---------------|
| Clamping area for laminated copper bars for 10 mm bar thickness, (W x H) | 65 x 22 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 0.199 |
| Gross weight | 1.271 |
| Copper weight (kg per piece) | 0.136 |
| Customs tariff number | 85369010 |
| EAN | 4028177536876 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| Approvals | ABS |
|--------------|------------------------------|
| | DNV-GL |
| | Lloyds Register of Shipping |
| | UL + C-UL (listed) |
| Explanations | Declaration of conformity |
| | Declaration of conformity UK |

© Rittal 2025 3