

Rittal – The System.

Faster – better – everywhere.



AX 9208.100 Ex Enclosures

State: 2026-02-13 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 9208.100 - Ex Enclosures Fiberglass Reinforced Polyester AX, empty enclosure with hinged door

Ex enclosure with hinged door, fiberglass-reinforced polyester



Features

Model No.	AX 9208.100
Version	Ex Enclosures
Applications	<p>Zone 1 and 2 or 21 and 22 to 2014/34/EU Ambient temperature range: -40 °C...+70 °C The specified temperatures can be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection due to increased safety (Ex e), equipment protection due to enclosure (Ex tb)</p>
Material	<p>Housing: fiber-glass reinforced unsaturated polyester, surface resistance: < 10\times Ω Door: glass fiber reinforced unsaturated polyester, surface resistance: < 10\times Ω circumferentially bonded silicone gasket Mounting plate: Carbon steel, zinc-plated</p>
Color	RAL 9011
Supply includes	<p>Housing Door Mounting panel</p>

Features

Dimensions	Width: 600 mm Height: 800 mm Depth: 300 mm
Dimensions of mounting plate (W x H)	505 mm x 725 mm
Material thickness – mounting plate	3 mm
Certificate IEC EX PTB 10.0011U	Yes
Certificate PTB 03 ATEX 1011U	Yes
Lock	No. of locks: 3
Protection category IP to IEC 60 529	IP 65
Protection category NEMA	Type 1 Type 3R Type 3RX Type 4 Type 4X Type 12
IK code	IK09
Operating temperature range	-40 °C...70 °C
Operating temperature	The specified temperatures can be limited by the installed equipment
Packaging unit	1 pc(s).
Net weight	26
Gross weight	26.5
Customs tariff number	94037000
EAN	4028177952126
ETIM 9	EC002503
ECLASS 8.0	27180502

Approvals

Approvals	ATEX ATEX QA IECEx IECEx QAR UR + C-UR (recognized)
Explanations	Attestation of Conformity
