

Rittal – The System.

Faster – better – everywhere.



SV 9342.504

Circuit-Breaker Component Adaptors

State: 2026-05-26 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9342.504 - Circuit-Breaker Component Adaptors 4-pole

Features

Model No.	SV 9342.504
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Supply includes	Terminal cover Sliding Blocks
Type of connection (electrical)	Box terminal
Rated current max.	160 A
Rated operating voltage	690 V, 4~
Electrical UL ratings (SCCR)	65 kA - 480 V, circuit breaker max. 125 A, DIVQ/7
Cable outlet	Top
For bar systems with center-to-center spacing	60 mm
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications.
Number of poles	4-pole
Dimensions	Width: 120 mm Height: 277 mm
Connection of round conductors	35 - 120 mm ²
Suitable for busbars	Height: 5, 10 mm
Clamping area for laminated copper bars (W x H)	18.5 x 15.5 mm
To fit manufacturer (model)	ABB (T1, T2, XT1, XT2) Eaton (NZM1-4/125 A, BZM E1-4/100 A) Schneider Electric (NSC100) Schrack (MC1) Siemens (3VA10, 3VA11)

Features

Approvals	UL
Packaging unit	1 pc(s).
Net weight	1.225 kg
Gross weight	1.425 kg
Copper weight (kg per piece)	0.258
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Circuit-breaker component adaptor, 160 A, 690 V, 4-pole, cable outlet top, round conductor connection 35-120 mm ² , clamping area WH: 18,5x15,5 mm

Approvals

Approvals	ABS Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK