Rittal - The System.

Faster – better – everywhere.





SV 9343.030 NH Fuse-Switch Disconnectors

State: 2025-11-02 (Source: rittal.com/ca-en)



SV 9343.030 - NH Fuse-Switch Disconnectors With electronic fuse monitoring

Features

Model No.	SV 9343.030
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 20 mm Clamping area height: 5 mm
For bar systems with center-to- center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M8
Rated operating current max.	160 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm
Connection of round conductors	10 - 95 mm²
Suitable for busbars	Height: 5, 10 mm
Number of poles	3-pole
With electronic fuse monitoring	Yes
Packaging unit	1 pc(s).

© Rittal 2025

Features

Net weight	0.927
Gross weight	1.029
Copper weight (kg per piece)	0.2
Customs tariff number	85369095
EAN	4028177540293
ETIM 9	EC000249
ECLASS 8.0	27371401

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3