

Rittal – The System.

Faster – better – everywhere.



KEL 9304.000

Ex Enclosures

State: 2026-02-07 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

KEL 9304.000 - Ex Enclosures Stainless steel, empty enclosure with screw fastened cover

Ex Housings with Screw-Fastened Cover, Stainless Steel



Features

Model No.	KEL 9304.000
Version	Ex Enclosures
Applications	<p>Zone 1 and 2 or 21 and 22 to 2014/34/EU Ambient temperature range: -30 °C...+80 °C The specified temperatures can be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection due to increased safety (Ex e), equipment protection due to enclosure (Ex tb)</p>
Material	<p>Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal</p>
Surface finish	Housing: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Housing Cover
Dimensions	<p>Width: 300 mm Height: 200 mm Depth: 80 mm</p>
Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Base material	Stainless steel 1.4301 (AISI 304)

Features

Protection category IP to IEC 60

529

IP 66

Packaging unit

1 pc(s).

Net weight

2.4

Gross weight

2.44

Customs tariff number

94032080

EAN

4028177138605

ETIM 9

EC002503

ECLASS 8.0

27180502

Approvals

Approvals

ATEX

ATEX QA

CQC-CCC

IECEx

IECEx QAR

Explanations

Attestation of Conformity