


Rittal – The System.

Faster – better – everywhere.



SV 9343.050

NH Fuse-Switch Disconnectors

State: 2025-08-30 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9343.050 - NH Fuse-Switch Disconnectors with electromechanical fuse monitoring

Features

Model No.	SV 9343.050
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 20 mm Clamping area height: 5 mm
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M8
Rated operating current max.	160 A
Rated operating voltage	690 V, 3~
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm
Connection of round conductors	10 - 95 mm ²
Suitable for busbars	Height: 5, 10 mm
Number of poles	3-pole
Packaging unit	1 pc(s).
Net weight	1.3

Features

Gross weight	1.311
Copper weight (kg per piece)	0.2
Customs tariff number	85365080
EAN	4028177540316
ETIM 9	EC000249
ECLASS 8.0	27371401

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK