

# Rittal – The System.

Faster – better – everywhere.



## SV 9343.130

## NH Fuse-Switch Disconnectors

State: 2025-08-15 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9343.130 - NH Fuse-Switch Disconnectors With electronic fuse monitoring

## Features

Model No.	SV 9343.130
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 32 mm Clamping area height: 10 mm
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
Rated operating current max.	250 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	1
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 184 mm Height: 298 mm
Connection of round conductors	10 - 150 mm <sup>2</sup>
Suitable for busbars	Height: 5, 10 mm
Number of poles	3-pole
With electronic fuse monitoring	Yes
Packaging unit	1 pc(s).

# Features

Net weight	2.498
Gross weight	2.505
Copper weight (kg per piece)	0.44
Customs tariff number	85369095
EAN	4028177540354
ETIM 9	EC000249
ECLASS 8.0	27371401

# Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK