Rittal - The System.

Faster – better – everywhere.





SV 9344.000 NH Fuse-Switch Disconnectors

State: 2025-10-16 (Source: rittal.com/ca-en)



SV 9344.000 - NH Fuse-Switch Disconnectors

Features

Model No.	SV 9344.000
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 13 mm Clamping area height: 13 mm
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal
Rated operating current max.	160 A
Rated operating voltage	690 V, 3~
For NH size	00
Note	The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses".
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm
Connection of round conductors	4 - 95 mm²
Number of poles	3-pole
Packaging unit	1 pc(s).
Net weight	0.7
Gross weight	0.74
Copper weight (kg per piece)	0.15

© Rittal 2025

Features

Customs tariff number	85369095
EAN	4028177540507
ETIM 9	EC000249
ECLASS 8.0	27371401

Approvals

Approvals	C-UR CQC-CCC UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3