

**Rittal – The System.**

Faster – better – everywhere.



**SV 9344.010**

**NH Fuse-Switch Disconnectors**

State: 2026-02-08 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))



FRIEDHELM LOH GROUP

# SV 9344.010 - NH Fuse-Switch Disconnectors

## Features

Model No.	SV 9344.010
Version	For mounting panel assembly.
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars: for mounting plate assembly	Clamping area width: 20 mm Clamping area height: 5 mm Yes
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M8
Rated operating current max.	160 A
Rated operating voltage	690 V, 3~
For NH size	00
Note	The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses".
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm
Connection of round conductors	10 - 95 mm <sup>2</sup>
Number of poles	3-pole
Round conductor cross-section	10 - 95 mm <sup>2</sup>
Packaging unit	1 pc(s).
Net weight	0.74

## Features

---

Gross weight	0.76
Copper weight (kg per piece)	0.15
Customs tariff number	85369095
EAN	4028177540514
ETIM 9	EC000249
ECLASS 8.0	27371401

## Approvals

---

Approvals	C-UR CQC-CCC UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK