

Rittal – The System.

Faster – better – everywhere.



SV 9340.410 OM adapter

State: 2026-05-12 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.410 - OM adapter with Connection Cables



Features

| | |
|---|---|
| Model No. | SV 9340.410 |
| Version | With connection cable |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | Chassis: RAL 7035 |
| Connection cables (AWG) | AWG 6 |
| Rated current max. | 65 A |
| Rated operating voltage | 690 V, 3~ |
| Electrical UL ratings (SCCR) | 30 kA - 600 V, fuse class K5 max. 60 A, JDDZ/7 30 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 65 kA - 600 V, fuse class J max. 60 A, JDDZ/7 65 kA - 480 V, manual motor controller max. 63 A, NLRV/7 65 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 |
| For bar systems with center-to-center spacing | 60 mm |
| Length of connection cable | 130 mm |
| Support rail type | Without support frame, 1 x TS 55E |
| Note | The technical data may vary for UL applications. |
| Number of poles | 3-pole |
| Dimensions | Width: 55 mm Height: 208 mm |

Features

| | |
|------------------------------|--|
| Support rails Qty/height | 1 / 10 mm |
| Suitable for busbars | Height: 5, 10 mm |
| Approvals | UL |
| Packaging unit | 1 pc(s). |
| Net weight | 0.317 kg |
| Gross weight | 0.36 kg |
| Copper weight (kg per piece) | 0.116 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV OM adaptor, 65 A, 690 V, 3-pole, connection cable AWG 6, WH: 55x208 mm, support rail TS 55E |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV Lloyds Register UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |