

# Rittal – The System.

Faster – better – everywhere.



## SV 9344.030

## NH Fuse-Switch Disconnectors

State: 2025-08-18 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9344.030 - NH Fuse-Switch Disconnectors With electronic fuse monitoring

## Features

Model No.	SV 9344.030
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 20 mm Clamping area height: 5 mm
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M8
Rated operating current max.	160 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm
Connection of round conductors	10 - 95 mm <sup>2</sup>
Number of poles	3-pole
With electronic fuse monitoring	Yes
Packaging unit	1 pc(s).
Net weight	0.7
Gross weight	0.835

# Features

Copper weight (kg per piece)	0.15
Customs tariff number	85369095
EAN	4028177540538
ETIM 9	EC000249
ECLASS 8.0	27371401

# Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK