

Rittal – The System.

Faster – better – everywhere.



SV 9344.210

NH Fuse-Switch Disconnectors

State: 2026-02-08 (Source: rittal.com/ca-en)



FRIEDHELM LOH GROUP

SV 9344.210 - NH Fuse-Switch Disconnectors

Features

Model No.	SV 9344.210
Version	For mounting panel assembly.
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars: for mounting plate assembly	Clamping area width: 50 mm Clamping area height: 10 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
Rated operating current max.	400 A
Rated operating voltage	690 V, 3~
For NH size	2
Note	The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses".
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 210 mm Height: 298 mm
Connection of round conductors	10 - 240 mm ²
Number of poles	3-pole
Round conductor cross-section	10 - 240 mm ²
Packaging unit	1 pc(s).
Net weight	3.08

Features

Gross weight	3.098
Copper weight (kg per piece)	1
Customs tariff number	85369095
EAN	4028177540675
ETIM 9	EC000249
ECLASS 8.0	27371401

Approvals

Approvals	C-UR CQC-CCC UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK