

Rittal – The System.

Faster – better – everywhere.



SV 9340.610 OM adapter

State: 2025-07-14 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.610 - OM adapter with tension spring clamp



Features

| | |
|---|--|
| Model No. | SV 9340.610 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | Chassis: RAL 7035 |
| Rated current max. | 65 A |
| Rated operating voltage | 690 V, 3~ |
| For bar systems with center-to-center spacing | 60 mm |
| Support rail type | TS 55E |
| Number of poles | 3-pole |
| Note on Model No.: | According to a heat dissipation test to IEC 61 439-1, a current carrying capacity of up to 80 A is supported |
| Dimensions | Width: 55 mm Height: 208 mm |
| Connection of round conductors | 2.5 - 16 mm ² |
| Support rails Qty/height | 1 / 10 mm |
| Suitable for busbars | Height: 5, 10 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 0.24 |

Features

| | |
|------------------------------|---------------|
| Gross weight | 0.324 |
| Copper weight (kg per piece) | 0.059 |
| Customs tariff number | 85369095 |
| EAN | 4028177502659 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV-GL Lloyds Register of Shipping |
| Explanations | Declaration of conformity Declaration of conformity UK |