


Rittal – The System.

Faster – better – everywhere.



SV 9345.005

Fuse Holders

State: 2026-02-13 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.005 - Fuse Holders 31 A to 60 A

Fuse holder up to 60 A, 3-pole. Simple mounting on support rails or via OM component adapters.

Features

Model No.	SV 9345.005
Version	For class CC fuse type
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Connection for round conductor	AWG 8 - 18
For fuse type (class)	CC
Rated operating current max.	30 A
Rated operating voltage	600 V, 3~
Fuse standard	UL 248-4
Note	For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adapter combinations (OM adapters/supports)
Test specification	UL 4248-1 UL 4248-4 UL 4248-8
Note on Model No.:	Not suitable for 10 x 38 mm fuses as per IEC 60 269-2/-4/-6
Dimensions	Width: 54 mm Height: 81 mm
Connection of round conductors	0.75 - 25 mm ²
Suitable for fuses	Diameter: 10 mm Length: 38 mm
Voltage range for indicator lights	110 - 600 V
Electrical UL ratings (SCCR)	200 kA - 600 V, fuse class CC max. 30 A, JDDZ/7
Number of poles	3-pole

Features

Round conductor cross-section	0.75 - 25 mm ²
Packaging unit	4 pc(s).
Net weight	0.4
Gross weight	0.634
Copper weight (kg per piece)	0.018
Customs tariff number	85369095
EAN	4028177805385
ETIM 9	EC001644
ECLASS 8.0	27400613

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK
