

Rittal – The System.

Faster – better – everywhere.



SV 9345.200 Fuse Holders

State: 2025-12-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.200 - Fuse Holders 61 A to 400 A

3-pole, for busbar systems with 60 mm bar center distance.

Features

| | |
|---|--|
| Model No. | SV 9345.200 |
| Version | For fuse type class J |
| Material | Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Electrolytic copper, silver-plated |
| Color | Chassis: RAL 7035 Cover: RAL 7035/7001 |
| Connection for round conductor | AWG 4/0 – MCM 600 |
| For bar systems with center-to-center spacing | 60 mm |
| Cable outlet | Top/bottom |
| Type of connection (electrical) | Box terminal |
| For fuse type (class) | J |
| Rated operating current max. | 200 A |
| Rated operating current (min.) | 101 A |
| Rated operating voltage | 600 V, 3~ |
| Fuse standard | UL 248-8 |
| Note | UL (listed accessory) is met through use of the fuse holder on RiLine busbar systems |
| Standards | UL 508 |
| Dimensions | Width: 210 mm Height: 288 mm |
| Suitable for fuses | Diameter: 41 mm Length: 146 mm |
| Suitable for busbars | Height: 5, 10 mm |

Features

| | |
|------------------------------|---|
| Electrical UL ratings (SCCR) | 100 kA - 600 V, fuse class J max. 200 A, JDDZ/7 |
| Number of poles | 3-pole |
| Packaging unit | 1 pc(s). |
| Net weight | 3.939 |
| Gross weight | 3.94 |
| Copper weight (kg per piece) | 1.389 |
| Customs tariff number | 85369095 |
| EAN | 4028177615663 |
| ETIM 9 | EC001644 |
| ECLASS 8.0 | 27400613 |

Approvals

| | |
|-----------|--|
| Approvals | C-UR UL + C-UL (listed) UR + C-UR (recognized) |
|-----------|--|