

Rittal – The System.

Faster – better – everywhere.



SV 9340.730 OM adapter

State: 2025-07-01 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.730 - OM adapter with Connection Cables



Features

Model No.	SV 9340.730
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
Connection cables (AWG)	AWG 8
Rated current max.	40 A
Rated operating voltage	690 V, 3~
Electrical UL ratings (SCCR)	30 kA - 600 V, fuse class K5 max. 60 A, JDDZ/7 30 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 65 kA - 600 V, fuse class J max. 60 A, JDDZ/7 65 kA - 480 V, manual motor controller max. 63 A, NLRV/7 65 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7
For bar systems with center-to-center spacing	60 mm
Length of connection cable	130 mm
Support rail type	TS 55D TS 55D-V
Note	The technical data may vary for UL applications.
Number of poles	3-pole
Support frame support	Yes

Features

Dimensions	Width: 55 mm Height: 272 mm
Support rails Qty/height	2 / 10 mm
Suitable for busbars	Height: 5, 10 mm
Support frame (W x H)	55 mm x 237 mm
Packaging unit	1 pc(s).
Net weight	0.36
Gross weight	0.382
Copper weight (kg per piece)	0.088
Customs tariff number	85369095
EAN	4028177664258
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK