Rittal - The System.

Faster – better – everywhere.





SV 9345.704 Circuit-Breaker Component

Adaptors

State: 2025-11-18 (Source: rittal.com/ca-en)



SV 9345.704 - Circuit-Breaker Component Adaptors 4-pole

Features

Model No.	SV 9345.704
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Supply includes	Roll of copper Connection screws Contact plates
Rated current max.	500 A
Rated operating voltage	690 V, 4~
Cable outlet	Bottom
For bar systems with center-to- center spacing	60 mm
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgea The technical data may vary for UL applications.
Number of poles	4-pole
Dimensions	Width: 185 mm Height: 300 mm
Suitable for busbars	Height: 5, 10 mm
To fit manufacturer (model)	ABB (Tmax T5)
Packaging unit	1 pc(s).
Net weight	3.98
Gross weight	4.027
Copper weight (kg per piece)	2.765
Customs tariff number	85369095
EAN	4028177684515

© Rittal 2025

Features

ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3