

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.780 OM adapter

State: 2026-07-03 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.780 - OM adapter with Connection Cables

## Features

|   |   |
|---|---|
| Model No.                                     | SV 9340.780   |
| Version                                       | With connection cable   |
| Material                                      | Polyamide<br>Fire protection corresponding to UL 94-V0  |
| Color   | Chassis: RAL 7035   |
| Connection cables (AWG)                       | AWG 12  |
| Rated current max.                            | 16 A  |
| Rated operating voltage                       | 690 V, 3~   |
| Note  | The technical data may vary for UL applications.  |
| Electrical UL ratings (SCCR)                  | 30 kA - 600 V, fuse class K5 max. 60 A, JDDZ/7<br>50 kA - 600 V, fuse class K5 max. 35 A, JDDZ/7<br>65 kA - 600 V, fuse class J max. 30 A, JDDZ/7<br>65 kA - 600 V, fuse class K5 max. 30 A, JDDZ/7<br>50 kA - 480 V, Combination Motor Controller max. 27 A, NKJH/7<br>65 kA - 480 V, Combination Motor Controller max. 32 A, NKJH/7 |
| For bar systems with center-to-center spacing | 60 mm   |
| Length of connection cable                    | 165 mm  |
| Support rail type                             | Support frame, 1 x TS 45D, 1 x TS 45D-V   |
| Number of poles                               | 3-pole  |
| Dimensions                                    | Width: 45 mm<br>Height: 208 mm  |
| Support rails Qty/height                      | 2 / 10 mm   |
| Suitable for busbars                          | Height: 5, 10 mm  |
| Support frame (W x H)                         | 45 mm x 170 mm  |
| Approvals                                     | UL  |

# Features

---

|                              |  |
|------------------------------|--|
| Packaging unit               | 1 pc(s).   |
| Net weight                   | 0.25 kg  |
| Gross weight                 | 0.3 kg   |
| Copper weight (kg per piece) | 0.038  |
| Customs tariff number        | 85369095   |
| ETIM 9                       | EC001531   |
| ECLASS 8.0                   | 27370304   |
| Product description          | SV OM adaptor, 16 A, 690 V, 3-pole, connection cable AWG 12, WH: 45x208 mm, support frame, support rail TS 45D, TS 45D-V |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | ABS<br>Lloyds Register<br>UL + C-UL (listed)              |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |