Rittal – The System.

Faster – better – everywhere.





RX 9360.000 RiLineX baying set

State: 2025-11-02 (Source: rittal.com/ca-en)



RX 9360.000 - RiLineX baying set for board

RiLineX baying connector set for the complete board, can be used for 550 A and 800 A. Consists of rail connector and contact hazard protection cover. For simple, drill-free baying of boards between two bayed VX enclosures.

Features

Model No.	RX 9360.000
Benefits	Time saving through complete digital product data
	Shorter mounting time thanks to pre-mounted complete board
	Tested short circuit resistance up to max. 65 kA
	Suitable for applications in the alternating current range up to 1,000
	V AC and direct current up to 1,500 V DC
	Contact hazard protection up to IP 2XB, can be upgraded to IP 3X
	Tested and certified according to IEC and UL
	Simple expansion and field alignment
Material	Upper part: carbon steel, zinc-plated
	Contact plate: E-Cu, tin-plated
	Front cover: polyamide (PA 6)
	Fire behavior corresponding to UL 94
Color	RAL 35745
Supply includes	3 rail connectors
	1 front cover
	1 insulating plate
Protection category IP to IEC 60 529	IP 2XB
Standards	IEC 61 439-1/-2
	UL 508
Rated current max.	780 A
Rated current (UL)	780 A

© Rittal 2025 2

Features

Electrical UL ratings (SCCR)	52.5 kA - 600 V, RMS 100 kA - 600 V, fuse class L max. 1600 A, JDDZ/7 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Rated impulse withstand voltage UImp	12 kV
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Rated insulation voltage	1,000 V AC 1,500 V DC
Rated impulse withstand current	103 kA 115.5 kA
Rated short-time withstand current/t	45 kA/200 ms 52.5 kA/500 ms
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Fundamental frequency	5060 Hz
Ambient humidity (non-condensing)	1090 %
Suitable for busbars	30 x 5/10
Operating temperature range	-5 °C55 °C
Dimensions	Width: 153 mm Height: 240 mm Depth: 77 mm
Packaging unit	1 pc(s).
Net weight	1.88
Gross weight	1.924
Copper weight (kg per piece)	0.297

© Rittal 2025 3

Features

Customs tariff number	85369010
EAN	4028177997431
ETIM 9	EC002270

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025