


Rittal – The System.

Faster – better – everywhere.



RX 9360.004

RiLineX Board

State: 2026-01-10 (Source: rittal.com/ca-en)



FRIEDHELM LOH GROUP

RX 9360.004 - RiLineX Board

Complete board 550 A, 905 mm for 1,000 mm wide enclosures.

Features

Model No.	RX 9360.004
Benefits	<p>Time saving through complete digital product data</p> <p>Shorter mounting time thanks to pre-mounted complete board</p> <p>Suitable for applications in the alternating current range up to 1,000 V AC and direct current up to 1,500 V DC</p> <p>Tested short circuit resistance up to max. 65 kA</p> <p>Contact hazard protection up to IP 2XB, can be upgraded to IP 3X</p> <p>Tested and certified according to IEC and UL</p> <p>Simple expansion and field alignment</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire behavior corresponding to UL 94</p> <p>E-Cu</p>
Color	<p>RAL 35745</p> <p>RAL 9005</p>
Supply includes	Including integrated busbars
Protection category IP to IEC 60 529	IP 2XB
Standards	<p>IEC 61 439-1/-2</p> <p>UL 508</p>
Rated current max.	550 A
Rated current (UL)	540 A
Electrical UL ratings (SCCR)	<p>45 kA - 600 V, RMS, unprotected</p> <p>100 kA - 600 V, fuse class L max. 1600 A, JDDZ/7</p> <p>100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7</p> <p>100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7</p> <p>65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7</p>
Center-to-center spacing of busbars	60 mm

Features

Rated impulse withstand voltage UImp	12 kV
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Rated insulation voltage	1,000 V AC 1,500 V DC
Rated impulse withstand current	115.5 kA 94.5 kA (UL)
Rated short-time withstand current/t	45 kA/500 ms
Overvoltage category	4
Contamination level	3
Busbar dimensions	30 mm x 5 mm
Number of poles	3-pole
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 905 mm Height: 246 mm Depth: 49 mm Length: 905 mm
Packaging unit	1 pc(s).
Net weight	7.9
Gross weight	8.445
Copper weight (kg per piece)	3.612
Customs tariff number	85369010
EAN	4028177997424

Features

ETIM 9

EC001900

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity