

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.535

## RiLineX CB device adapter

State: 2026-01-02 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.535 - RiLineX CB device adapter

RiLineX CB device adapter (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 145 mm. Thanks to the Easy-Fix concept, adapter and switch installation can be carried out independently of each other. This concept is available for all popular manufacturers. The adapter has tool-free snap-on mounting with semi-automatic adjustment of the rail thickness between 5 and 10 mm. The cable outlet can be adapted to individual requirements by simply converting the outlet at the bottom or top.



## Features

Model No.	RX 9360.535
Version	Easy Fix
Benefits	Direct mounting of compact circuit breaker MCCB on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Quick and easy pre-assembly of standard switch types outside the control cabinet
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Supply includes	Incl. 3 clamp covers
Protection category IP to IEC 60 529	IP 2XB
Rated impulse withstand voltage UImp	12 kV

# Features

Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage	1,000 V
Overvoltage category	4
Contamination level	3
Clamping area for laminated copper bars (W x H)	29 x 10 mm
Number of poles	3-pole
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
To fit manufacturer (model)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
Suitable for busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 145 mm Height: 325.8 mm Depth: 76.4 mm
Packaging unit	1 pc(s).
Net weight	5
Gross weight	5.206
Copper weight (kg per piece)	2.64

# Features

Customs tariff number	85369095
EAN	4028177997110
ETIM 9	EC001531

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity