

Rittal – The System.

Faster – better – everywhere.



SV 9343.010

NH Fuse-Switch Disconnectors

State: 2026-01-12 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9343.010 - NH Fuse-Switch Disconnectors

Features

Model No.	SV 9343.010
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 20 mm Clamping area height: 5 mm
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M8
Rated operating current max.	160 A
Rated operating voltage	690 V, 3~
For NH size	00
Note	The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses".
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm
Connection of round conductors	10 - 95 mm ²
Suitable for busbars	Height: 5, 10 mm
Number of poles	3-pole
Round conductor cross-section	10 - 95 mm ²
Packaging unit	1 pc(s).

Features

Net weight 0.84

Gross weight 0.94

Copper weight (kg per piece) 0.2

Customs tariff number 85369095

EAN 4028177540262

ETIM 9 EC000249

ECLASS 8.0 27371401

Approvals

Approvals C-UR
CQC-CCC
UR + C-UR (recognized)

Explanations Declaration of conformity
Declaration of conformity UK