## Rittal - The System.

Faster – better – everywhere.





# RX 9360.535 RiLineX CB device adapter

State: 2025-11-03 (Source: rittal.com/ca-en)



#### RX 9360.535 - RiLineX CB device adapter

RiLineX CB device adapter (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 140 mm. Thanks to the Easy-Fix concept, adapter and switch installation can be carried out independently of each other. This concept is available for all popular manufacturers. The adapter has tool-free snap-on mounting with semi-automatic adjustment of the rail thickness between 5 and 10 mm. The cable outlet can be adapted to individual requirements by simply converting the outlet at the bottom or top.



#### **Features**

Model No.	RX 9360.535
Version	Easy Fix
Benefits	Direct mounting of compact circuit breaker MCCB on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Quick and easy pre-assembly of standard switch types outside the control cabinet
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Supply includes	Incl. 3 clamp covers
Protection category IP to IEC 60 529	IP 2XB
Rated impulse withstand voltage Ulmp	12 kV

© Rittal 2025 2

### **Features**

Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage	1,000 V
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
To fit manufacturer (model)	ABB (S5 400, S5, T5, XT5, FG400, FG630) Chint (NM8N-400, NM8N-630, NXM-400S, NXM-630S, NXMS-400, NXMS-630) Eaton (NZM3) Fuji Electric (BW4003) Hager (X630) Hyundai Electric (400AF, 400, 630AF) LS Electric (400AF, TS400, TS630) Mitsubishi (NF400-SW, NF630-SW) OEZ (BH630) Rockwell (140G-K0F3-D40, 140G-M0F3-D63) Schneider (NSX400, NSX630) Schrack (MC3) Siemens (3VA23, 3VA24) Terasaki (S400, E630, S630)
Suitable for busbar system	RiLineX RiLine60
Fundamental frequency	5060 Hz
Ambient humidity (non- condensing)	1090 %
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C55 °C

© Rittal 2025 3

## Features

Dimensions	Width: 145 mm Height: 325 mm
Packaging unit	1 pc(s).
Net weight	5
Gross weight	5.206
Copper weight (kg per piece)	2.64
Customs tariff number	85369095
EAN	4028177997110
ETIM 9	EC001531

## **Approvals**

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025