

Rittal – The System.

Faster – better – everywhere.



SV 9343.020

NH Fuse-Switch Disconnectors

State: 2026-05-30 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9343.020 - NH Fuse-Switch Disconnectors With electronic fuse monitoring

Features

Model No.	SV 9343.020
Version	For 60 mm busbar systems
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 13 mm Clamping area height: 13 mm
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal
Rated operating current max.	160 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm
Connection of round conductors	4 - 95 mm ²
Suitable for busbars	Height: 5, 10 mm
Number of poles	3-pole
With electronic fuse monitoring	Yes

Features

Round conductor cross-section	4 - 95 mm ²
Packaging unit	1 pc(s).
Net weight	1 kg
Gross weight	1.02 kg
Copper weight (kg per piece)	0.2
Customs tariff number	85369095
ETIM 9	EC000249
ECLASS 8.0	27371401
Product description	SV NH fuse-switch disconnecter, size 00, 160 A, 400-690 V, 3-pole, box terminal, with electronic fuse monitoring

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK