

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.635 RiLineX CB device adapter

State: 2025-12-07 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.635 - RiLineX CB device adapter

RiLineX CB device adapter (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 145 mm. The "universal" version with sliding nuts offers maximum flexibility for switch installation. The adapter has tool-free snap-on mounting with semi-automatic adjustment of the rail thickness between 5 and 10 mm. The cable outlet can be adapted to individual requirements by simply converting the outlet at the bottom or top.



## Features

|  |  |
|--|--|
| Model No.  | RX 9360.635  |
| Version  | universal  |
| Benefits   | Direct mounting of compact circuit breaker MCCB on the board<br>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm<br>Quick and easy pre-assembly of standard switch types outside the control cabinet |
| Material   | Polyamide (PA 6)<br>Fire behavior corresponding to UL 94   |
| Color  | RAL 9005<br>RAL 35745  |
| Supply includes                                  | Incl. 3 connection compartment covers, 2 crossbars and fastening material  |
| Protection category IP to IEC 60 529             | IP 2XB   |
| Rated impulse withstand voltage U <sub>Imp</sub> | 12 kV  |

# Features

|   |   |
|---|---|
| Rated voltage                                   | 690 V AC<br>690 V DC<br>600 V AC (UL)   |
| Rated insulation voltage                        | 1,000 V   |
| Overvoltage category                            | 4   |
| Contamination level                             | 3   |
| Clamping area for laminated copper bars (W x H) | 29 x 10 mm  |
| Number of poles                                 | 3-pole  |
| Cable outlet                                    | Top/bottom  |
| Type of connection (electrical)                 | Screw M10   |
| To fit manufacturer (model)                     | Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor. |
| Suitable for busbar system                      | RiLineX<br>RiLine60   |
| Fundamental frequency                           | 50...60 Hz  |
| Ambient humidity (non-condensing)               | 10...90 %   |
| Suitable for busbars                            | 15 x 5/10<br>20 x 5/10<br>30 x 5/10   |
| Operating temperature range                     | -25 °C...55 °C  |
| Storage temperature range                       | -25 °C...75 °C  |
| Dimensions                                      | Width: 145 mm<br>Height: 325.8 mm<br>Depth: 76.4 mm   |
| Packaging unit                                  | 1 pc(s).  |
| Net weight                                      | 4.52  |
| Gross weight                                    | 4.722   |
| Copper weight (kg per piece)                    | 2.64  |

# Features

|                       |               |
|-----------------------|---------------|
| Customs tariff number | 85369095      |
| EAN                   | 4028177997066 |
| ETIM 9                | EC001531      |

# Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |