

Rittal – The System.

Faster – better – everywhere.



RX 9360.730 RiLineX device adapter

State: 2026-06-10 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.730 - RiLineX device adapter

Component adapter 45 mm. Snap-on mounting of components.



Features

Model No.	RX 9360.730
Version	With connection cable
Benefits	For mounting equipment for top-hat rail mounting, e.g. motor starter Pre-assembled connection cable Simple connector lock for component support rails Optional component anti-slip guard Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Easy mounting Reduction of article variety through coordinated accessories
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Connection cables (AWG)	AWG 10
Rated current (max.)	40 A
Rated current of round conductor	40 A
Rated current round conductor (UL)	40 A

Features

Cable outlet	Bottom
For bar systems with center-to-center spacing	60 mm
Length of connection cable	160 mm
Number of poles	3-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 45 mm Height: 239.4 mm Depth: 36.2 mm
Support rails Qty/height	1 / 10 mm
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
Rated impulse withstand voltage U _{Imp}	8 kV
Rated insulation voltage U _i	1,000 V
Protection category IP to IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Packaging unit	4 pc(s).

Features

Net weight	1.42 kg
Gross weight	1.45 kg
Copper weight (kg per piece)	0.088
PCF/VE (cradle-to-gate)	9.34
Customs tariff number	85369095
ETIM 9	EC001531
Product description	RX component adapter 32 A, AWG 10, 3-pole, W: 45 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration