Rittal – The System.

Faster – better – everywhere.





RX 9360.760 RiLineX device adapter

State: 2025-11-19 (Source: rittal.com/ca-en)



RX 9360.760 - RiLineX device adapter

Component adapter 54 mm. Snap-on mounting of components.



Features

Model No.	RX 9360.760	
Version	With connection cable	
Benefits	For mounting equipment for top-hat rail mounting, e.g. motor star Pre-assembled connection cable AWG 14 - 2 (16 A - 100 A) Simple connector lock for component support rails Optional component anti-slip guard Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Easy mounting Reduction of article variety through coordinated accessories	
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94	
Color	RAL 9005 RAL 35745	
Connection cables (AWG)	AWG 6	
Rated current of round conductor	65 A	
Rated current of round conductor (UL)	65 A	
Cable outlet	Тор	
For bar systems with center-to- center spacing	60 mm	
Length of connection cable	130 mm	

© Rittal 2025

Features

Number of poles	3-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 54 mm Height: 240 mm Depth: 37 mm
Support rails Qty/height	1 / 10 mm
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
Protection category IP to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C55 °C
Storage temperature range	-25 °C75 °C
Ambient humidity (non- condensing)	1090 %
Packaging unit	4 pc(s).
Net weight	1.84
Gross weight	1.883
Copper weight (kg per piece)	0.145
Customs tariff number	85369095

© Rittal 2025 3

Features

ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)	
Explanations	Declaration of conformity	

© Rittal 2025