

Rittal – The System.

Faster – better – everywhere.



RX 9360.760

RiLineX device adapter

State: 2026-01-20 (Source: rittal.com/ca-en)

RX 9360.760 - RiLineX device adapter

Component adapter 54 mm. Snap-on mounting of components.



Features

Model No.	RX 9360.760
Version	With connection cable
Benefits	<p>For mounting equipment for top-hat rail mounting, e.g. motor starter</p> <p>Pre-assembled connection cable AWG 14 - 2 (16 A - 100 A)</p> <p>Simple connector lock for component support rails</p> <p>Optional component anti-slip guard</p> <p>Snap-on mounting and easy adjustment on busbar thickness 5/10 mm</p> <p>Easy mounting</p> <p>Reduction of article variety through coordinated accessories</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire behavior corresponding to UL 94</p>
Color	<p>RAL 9005</p> <p>RAL 35745</p>
Connection cables (AWG)	AWG 6
Rated current of round conductor	65 A
Rated current of round conductor (UL)	65 A
Electrical UL ratings (SCCR)	<p>100 kA - 600 V, fuse class RK5 max. 60 A, JDDZ/7</p> <p>20 kA - 600 V, circuit breaker max. 60 A, DIVQ/7</p> <p>65 kA - 480 V, Combination Motor Controller max. 52 A, NKJH/7</p>
Cable outlet	Top

Features

For bar systems with center-to-center spacing	60 mm
Length of connection cable	130 mm
Number of poles	3-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 54 mm Height: 239.4 mm Depth: 36.2 mm
Support rails Qty/height	1 / 10 mm
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
Protection category IP to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Packaging unit	4 pc(s).
Net weight	1.84
Gross weight	1.883
Copper weight (kg per piece)	0.145

Features

Customs tariff number 85369095

EAN 4028177996991

ETIM 9 EC001531

Approvals

Approvals UL + C-UL (listed)

Explanations Declaration of conformity