Rittal – The System.

Faster – better – everywhere.





RX 9360.798 RiLineX device adapter

State: 2025-11-28 (Source: rittal.com/ca-en)



RX 9360.798 - RiLineX device adapter

Component adapter 72 mm, 100 A, with pre-mounted insert nuts for standard circuit-breakers.



Features

Model No.	RX 9360.798
Version	With connection cable
Benefits	For mounting equipment for top-hat rail mounting, e.g. motor starter Pre-assembled connection cable AWG 14 - 2 (16 A - 100 A) Simple connector lock for component support rails Optional component anti-slip guard Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Easy mounting Reduction of article variety through coordinated accessories
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Connection cables (AWG)	AWG 4
Rated current of round conductor	80 A
Rated current of round conductor (UL)	80 A
Cable outlet	Тор
For bar systems with center-to- center spacing	60 mm
Number of poles	3-pole

© Rittal 2025

Features

RiLineX
RiLine60
Width: 72 mm
Height: 239.4 mm
Depth: 36.6 mm
15 x 5/10
20 x 5/10
30 x 5/10
690 V AC
600 V AC (UL)
600 V DC (UL)
4
3
IEC 61 439-1/-2
UL 508
IP 2XB
90 %
-5 °C55 °C
-25 °C75 °C
1090 %
1 pc(s).
0.7
0.702
0.246
85369095
EC001531

© Rittal 2025 3

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025