

# Rittal – The System.

Faster – better – everywhere.



## SV 9343.200

## NH Fuse-Switch Disconnectors

State: 2026-02-12 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9343.200 - NH Fuse-Switch Disconnectors

## Features

Model No.	SV 9343.200
Version	For 60 mm busbar systems
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 32 mm Clamping area height: 10 mm
Note	Connection of sector-shaped conductors 120 - 300 mm <sup>2</sup>
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal
Rated operating current max.	400 A
Rated operating voltage	690 V, 3~
For NH size	2
Note	The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses".
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 210 mm Height: 298 mm
Connection of round conductors	95 - 300 mm <sup>2</sup>
Suitable for busbars	Height: 5, 10 mm

## Features

---

Clamping area for laminated copper bars:	20 mm
Number of poles	3-pole
Round conductor cross-section	95 - 300 mm <sup>2</sup>
Packaging unit	1 pc(s).
Net weight	3.42
Gross weight	3.62
Copper weight (kg per piece)	1
Customs tariff number	85369095
EAN	4028177540385
ETIM 9	EC000249
ECLASS 8.0	27371401

## Approvals

---

Approvals	C-UR CQC-CCC UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK