

Rittal – The System.

Faster – better – everywhere.



SV 9343.210

NH Fuse-Switch Disconnectors

State: 2026-01-11 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

SV 9343.210 - NH Fuse-Switch Disconnectors

Features

Model No.	SV 9343.210
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 50 mm Clamping area height: 10 mm
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
Rated operating current max.	400 A
Rated operating voltage	690 V, 3~
For NH size	2
Note	The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses".
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 210 mm Height: 298 mm
Connection of round conductors	10 - 240 mm ²
Suitable for busbars	Height: 5, 10 mm
Number of poles	3-pole
Round conductor cross-section	10 - 240 mm ²
Packaging unit	1 pc(s).

Features

Net weight 3.358

Gross weight 3.36

Copper weight (kg per piece) 1

Customs tariff number 85369095

EAN 4028177540392

ETIM 9 EC000249

ECLASS 8.0 27371401

Approvals

Approvals C-UR
CQC-CCC
UR + C-UR (recognized)

Explanations Declaration of conformity
Declaration of conformity UK