Rittal - The System.

Faster – better – everywhere.





RX 9360.802 RiLineX bus-mounting fuse element

State: 2025-12-02 (Source: rittal.com/ca-en)



RX 9360.802 - RiLineX bus-mounting fuse element

RiLineX bus-mounting fuse element for 60 mm busbar systems. For fuse D 01 (with fitting ring) and D 02 (E18). With optical LED fuse monitoring. For safe contacting of the fuse, the device does not have screw caps, but fuse holders that can be locked when open and sealed when closed. A tension clamp terminal up to 16 mm² at an angle of 45° facilitates conductor connection. The device is suitable for tool-free snap-on installation and has a semi-automatic rail adjustment for 5 and 10 mm.



Features

Model No.	RX 9360.802
Benefits	Safe contacting of the fuse links (without screw caps) Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm² Complete contact protection without additional accessories such as screw caps
Product modification	(secondary) (secondaire)
Material	Polyamide (PA 6) Fire protection corresponding to UL 94-V0
Color	RAL 35745 RAL 9005
Supply includes	4 bus-mounting fuse elements 12 reducers for D 01 fuses
Cable outlet	Bottom
Number of poles	3-pole

© Rittal 2025 2

Features

Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 26.8 mm Height: 253.8 mm Depth: 89.8 mm
Connection of round conductors, fine wire with wire end ferrule	1.5 - 16 mm²
Connection of round conductors, fine wire with wire end ferrule AWG	AWG 16 - AWG 6
Connection of round conductors, multi-wire	1.5 - 16 mm²
Connection of round conductors, multi-wire AWG	AWG 16 - AWG 6
Suitable for busbars	Height: 5, 10 mm
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	400 V AC
Overvoltage category	4
Contamination level	3
Standards	IEC 60 947-3
Rated insulation voltage	1,000 V
Power dissipation (max.)	5.5 W
Protection category IP to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C55 °C
Storage temperature range	-25 °C75 °C
Ambient humidity (non-condensing)	1090 %
Utilization category	AC-21B (400 V/100 A)

© Rittal 2025 3

Features

Fuse inserts	D 02-E 18
Packaging unit	4 pc(s).
Net weight	1.432
Gross weight	1.437
Copper weight (kg per piece)	0.07
Customs tariff number	85369095
ETIM 9	EC001644

Approvals

Explanations	Declaration of conformity
•	

© Rittal 2025