

Rittal – The System.

Faster – better – everywhere.



RX 9360.805

RiLineX bus-mounting fuse element

State: 2026-02-13 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

RX 9360.805 - RiLineX bus-mounting fuse element

RiLineX bus-mounting fuse element for 60 mm busbar systems. For fuse D 01 (with fitting ring) and D 02 (E18). With electronic and optical LED fuse monitoring via signaling contacts. For safe contacting of the fuse, the device does not have screw caps, but fuse holders that can be locked when open and sealed when closed. A tension clamp terminal up to 16 mm² at an angle of 45° facilitates conductor connection. The device is suitable for tool-free snap-on installation and has semi-automatic rail adjustment for 5 and 10 mm.



Features

| | |
|--------------------|--|
| Model No. | RX 9360.805 |
| Version | With electronic fuse monitoring |
| Benefits | <p>Safe contacting of the fuse links (without screw caps)</p> <p>Snap-on mounting and easy adjustment on busbar thickness 5/10 mm</p> <p>Optical LED fuse monitoring</p> <p>Voltage test through separate opening</p> <p>Maintenance-free tension spring connection up to 16 mm²</p> <p>Complete contact protection without additional accessories such as screw caps</p> |
| Product changes | <p>(secondary)</p> <p>(secondaire)</p> |
| Material | <p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94-V0</p> |
| Color | <p>RAL 35745</p> <p>RAL 9005</p> |
| Supply includes | <p>4 bus-mounting fuse elements</p> <p>12 reducers for D 01 fuses</p> |
| Rated current max. | 63 A |

Features

| | |
|---|--|
| Cable outlet | Bottom |
| Number of poles | 3-pole |
| Suitable for busbar system | RiLineX RiLine60 |
| Dimensions | Width: 35.8 mm Height: 253.8 mm Depth: 89.8 mm |
| Connection of round conductors, fine wire with wire end ferrule | 1.5 - 16 mm ² |
| Connection of round conductors, fine wire with wire end ferrule AWG | AWG 16 - AWG 6 |
| Connection of round conductors, multi-wire | 1.5 - 16 mm ² |
| Connection of round conductors, multi-wire AWG | AWG 16 - AWG 6 |
| Suitable for busbars | Height: 5, 10 mm |
| Suitable for busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Rated voltage | 400 V AC |
| Overvoltage category | 4 |
| Contamination level | 3 |
| Standards | IEC 60 947-3 |
| Rated insulation voltage Ui | 1,000 V |
| Power dissipation (max.) | 5.5 W |
| Protection category IP to IEC 60 529 | IP 2XB |
| Operation humidity max. | 90 % |
| Operating temperature range | -5 °C...55 °C |
| Storage temperature range | -25 °C...75 °C |

Features

Ambient humidity (non-condensing) 10...90 %

Utilization category AC-21B (400 V/100 A)

Fuse inserts D 02-E 18

Packaging unit 4 pc(s).

Net weight 1.796

Gross weight 1.8

Copper weight (kg per piece) 0.07

Customs tariff number 85369095

ETIM 9 EC001644

Approvals

Explanations Declaration of conformity