Rittal - The System.

Faster – better – everywhere.





SV 9343.300 NH Fuse-Switch Disconnectors

State: 2025-11-03 (Source: rittal.com/ca-en)



SV 9343.300 - NH Fuse-Switch Disconnectors

Features

SV 9343.300
Dalamaida
Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area width: 32 mm Clamping area height: 10 mm
Connection of sector-shaped conductors 120 - 300 mm ²
60 mm
Top/bottom
Box terminal
630 A
690 V, 3~
3
The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses".
IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Width: 250 mm Height: 298 mm
95 - 300 mm²
Height: 5, 10 mm
20 mm

© Rittal 2025

Features

Number of poles	3-pole
Packaging unit	1 pc(s).
Net weight	4.48
Gross weight	4.5
Copper weight (kg per piece)	1.44
Customs tariff number	85369095
EAN	4028177540446
ETIM 9	EC000249
ECLASS 8.0	27371401

Approvals

Approvals	C-UR
	CQC-CCC
	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3