


# Rittal – The System.

Faster – better – everywhere.



## RX 9360.825 RiLineX fuse switch disconnecter

State: 2026-05-25 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.825 - RiLineX fuse switch disconnecter D-switch

RiLineX fuse switch disconnecter for 60 mm busbar systems. For use with D 01 (via fitting ring) and D 02 fuses (max. 63 A). Also suitable for use with 10 x 38 mm cylinder locks using the retaining springs supplied. Integrated optical LED fuse monitoring. The switch can be locked in the on and off position. Tension clamp terminals up to 16 mm<sup>2</sup> at an angle of 45° make it easier to connect conductors. The device is suitable for tool-free snap-on installation with semi-automatic rail adjustment for 5 and 10 mm.



## Features

Model No.	RX 9360.825
Benefits	Safe contacting of the fuse links (without screw caps) Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm <sup>2</sup> Complete contact protection without additional accessories such as screw caps
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
General color	RAL 35745 RAL 9005
Supply includes	4 fuse switch disconnecters 12 reducers for D 01 fuses
Type of connection (electrical)	Spring terminal

# Features

Rated current max.	63 A
Rated operating voltage	400 V AC
Cable outlet	Bottom
Number of poles	3-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 26.8 mm Height: 263 mm Depth: 104.2 mm
Connection of round conductors	16 mm <sup>2</sup>
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Overvoltage category	4
Contamination level	3
Standards	IEC 60 947-3
Rated insulation voltage U <sub>i</sub>	800 V
Power loss max.	5.5 W
Protection category IP to IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Utilization category	AC-22B (400 V/100 A)
Fuse inserts	D 02-E 18
Packaging unit	4 pc(s).
Net weight	1.784 kg

# Features

---

Gross weight	1.792 kg
Copper weight (kg per piece)	0.105
PCF/VE (cradle-to-gate)	11.81
Customs tariff number	85365080
ETIM 9	EC001040
Product description	RX fuse switch disconnecter 63 A, 3-pole, with LED, W: 27 mm (D-switch)

# Approvals

---

Explanations	Declaration of conformity PCF-declaration
--------------	--