

Rittal – The System.

Faster – better – everywhere.



RX 9361.300

RiLineX connection adaptor

State: 2025-08-31 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9361.300 - RiLineX connection adaptor

Connection adapter RiLineX busbar platform. Suitable for double connection (bar). Freely selectable phase distance. Only suitable for 10 mm busbars.



Features

Model No.	RX 9361.300
Benefits	Mounting on the busbar system and cable connection with just one screw
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005
Rated current laminated copper bar	1,500 A
Rated current laminated copper bar (UL)	1,380 A
Electrical UL ratings (SCCR)	52.5 kA - 600 V, RMS 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 100 kA - 600 V, fuse class L max. 2000 A, JDDZ/7
Cable outlet	Top/bottom
For bar systems with center-to-center spacing	60 mm
Number of poles	1-pole
Suitable for busbar system	RiLineX RiLine60

Features

Dimensions	Width: 73 mm Height: 120 mm Depth: 120 mm
Clamping area for laminated copper bars (W x H)	50 x 10 mm
Suitable for busbars	15 x 10 20 x 10 30 x 10
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC/EN 61439-1 UL 508
Rated impulse withstand voltage U _{Imp}	12 kV
Rated insulation voltage	1,000 V
Protection category IP to IEC 60529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Packaging unit	1 pc(s).
Net weight	0.65
Gross weight	0.688
Customs tariff number	85369010
ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity