

Rittal – The System.

Faster – better – everywhere.



RX 9361.300

RiLineX connection adapter

State: 2026-02-14 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



RX 9361.300 - RiLineX connection adapter

Connection adapter RiLineX busbar platform. Suitable for double connection (bar). Freely selectable phase distance. Only suitable for 10 mm busbars.



Features

Model No.	RX 9361.300
Benefits	Mounting on the busbar system and cable connection with just one screw
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005
Rated current of laminated copper bar	1,500 A
Rated current of laminated copper bar (UL)	1,380 A
Electrical UL ratings (SCCR)	52,5 kA - 600 V, RMS, unprotected 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 100 kA - 600 V, fuse class L max. 2000 A, JDDZ/7
Cable outlet	Top/bottom
For bar systems with center-to-center spacing	60 mm
Number of poles	1-pole

Features

Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 72.3 mm Height: 119.4 mm Depth: 117.4 mm
Clamping area for laminated copper bars (W x H)	50 x 10 mm
Suitable for busbars	15 x 10 20 x 10 30 x 10
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC/EN 61439-1 UL 508
Rated impulse withstand voltage UImp	12 kV
Rated insulation voltage Ui	1,000 V
Protection category IP to IEC 60 529	IP 2XB
Operation humidity max.	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Packaging unit	1 pc(s).
Net weight	0.65
Gross weight	0.688

Features

Customs tariff number 85369010

ETIM 9 EC001531

Approvals

Approvals UL + C-UL (listed)

Explanations Declaration of conformity