### Rittal - The System.

Faster – better – everywhere.





# SV 9344.030 NH Fuse-Switch Disconnectors

State: 2025-11-17 (Source: rittal.com/ca-en)



# SV 9344.030 - NH Fuse-Switch Disconnectors With electronic fuse monitoring

#### **Features**

Model No.	SV 9344.030
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 20 mm Clamping area height: 5 mm
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M8
Rated operating current max.	160 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm
Connection of round conductors	10 - 95 mm²
Number of poles	3-pole
With electronic fuse monitoring	Yes
Cross section round conductor	10 - 95 mm²
Packaging unit	1 pc(s).
Net weight	0.7

© Rittal 2025

#### Features

Gross weight	0.835
Copper weight (kg per piece)	0.15
Customs tariff number	85369095
EAN	4028177540538
ETIM 9	EC000249
ECLASS 8.0	27371401

## **Approvals**

Approvals	CQC-CCC
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3