

Rittal – The System.

Faster – better – everywhere.



RX 9361.315 RiLineX connection adaptor

State: 2025-09-08 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9361.315 - RiLineX connection adaptor

Connection adapter RiLineX busbar platform. Suitable for double connection (round/sector-shaped conductor). Freely selectable phase distance. 1-pole for L1/L2/L3/N.



Features

Model No.	RX 9361.315
Benefits	Mounting on the busbar system and cable connection with just one screw
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005
Rated current round conductor	1,060 A
Rated current round conductor (UL)	980 A
Electrical UL ratings (SCCR)	27.5 kA - 600 V, RMS 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 600 V, fuse class L max. 2000 A, JDDZ/7
Cable outlet	Top/bottom
For bar systems with center-to-center spacing	60 mm
Number of poles	1-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 54 mm Height: 120 mm Depth: 165 mm

Features

Connection of round conductors	95 mm ²
Connection of round conductors, fine wire with wire end ferrule	95 - 300 mm ²
Connection of round conductors, fine wire with wire end ferrule AWG	AWG 3/0 - AWG 550
Connection of round conductors, multi-wire	95 - 300 mm ²
Connection of round conductors, multi-wire AWG	AWG 3/0 - AWG 550
Connection of sector-shaped conductors, single-wire	120 - 240 mm ²
Connection of sector-shaped conductors, single wire AWG	AWG 4/0 - AWG 450 kcmil
Connection of sector conductors, multi-wire	95 - 300 mm ²
Connection of sector-shaped conductors, multi-wire AWG	AWG 3/0 - AWG 550 kcmil
Suitable for busbars	15 x 10 20 x 10 30 x 10
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC/EN 61439-1 UL 508
Rated impulse withstand voltage U _{Imp}	12 kV
Rated insulation voltage	1,000 V
Power dissipation (max.)	105 W

Features

Protection category IP to IEC 60529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Packaging unit	1 pc(s).
Net weight	0.8
Gross weight	0.892
Customs tariff number	85369010
ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity