# Rittal - The System.

Faster – better – everywhere.





# RX 9362.000 RiLineX NH fuse switch disconnector

State: 2025-11-03 (Source: rittal.com/ca-en)



### RX 9362.000 - RiLineX NH fuse switch disconnector

RiLineX NH fuse-switch-disconnector in size 00 for 60 mm busbar systems. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnectors have a park position to simplify maintenance work. Connection version with size M8 screw connection. Cable outlet can be individually converted at the top or bottom.



### **Features**

Model No.	RX 9362.000
Benefits	Cover, lockable and sealable
	Voltage test through separate opening
	Snap-on mounting up to 250 A and simple adjustment to busbar
	thickness 5/10 mm
	Tool-free conversion of the cable outlet
	Park position for simplified maintenance work
	All variants also with electronic fuse monitoring
Material	Polyamide (PA 6)
	Fire behavior corresponding to UL 94
	Contact tracks: Electrolytic copper, silver-plated
Color	RAL 9005
	RAL 35745
For bar systems with center-to-	60 mm
center spacing	
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M8
Rated operating current max.	160 A
Rated operating voltage	690 V AC

© Rittal 2025 2

## Features

00
IEC 60 947-3
IEC 60 269-2 (fuse inserts)
Width: 106 mm
Height: 195 mm
Depth: 105 mm
-5 °C35 °C
-25 °C70 °C
15 x 5/10
20 x 5/10
30 x 5/10
RiLine60
RiLineX
3-pole
AC-23B (400 V/100 A)
AC-22B (500 V/100 A)
DC-22B (250 V/100 A)
3
IP 2XB
14.2 MJ/m²
19 W
1 pc(s).
1.015
1.023
0.363
85369095
EC001040

© Rittal 2025 3

# **Approvals**

Explanations

Declaration of conformity

© Rittal 2025