

Rittal – The System.

Faster – better – everywhere.



SV 9344.040

NH Fuse-Switch Disconnectors

State: 2026-01-20 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.040 - NH Fuse-Switch Disconnectors with electromechanical fuse monitoring

Features

| | |
|---|---|
| Model No. | SV 9344.040 |
| Version | For mounting panel assembly. |
| Material | Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated |
| Color | Chassis: RAL 7035 Cover: RAL 7035/7001 |
| Clamping area for laminated copper bars: for mounting plate assembly | Clamping area width: 13 mm Clamping area height: 13 mm Yes |
| Cable outlet | Top/bottom |
| Type of connection (electrical) | Box terminal |
| Rated operating current max. | 160 A |
| Rated operating voltage | 690 V, 3~ |
| For NH size | 00 |
| Test specification | IEC 60 947-3 IEC 60 269-2 (fuse inserts) |
| Dimensions | Width: 106 mm Height: 194 mm |
| Connection of round conductors | 4 - 95 mm ² |
| Number of poles | 3-pole |
| Round conductor cross-section | 4 - 95 mm ² |
| Packaging unit | 1 pc(s). |
| Net weight | 1.17 |

Features

| | |
|------------------------------|---------------|
| Gross weight | 1.172 |
| Copper weight (kg per piece) | 0.15 |
| Customs tariff number | 85369095 |
| EAN | 4028177540545 |
| ETIM 9 | EC000249 |
| ECLASS 8.0 | 27371401 |

Approvals

| | |
|--------------|---|
| Approvals | CQC-CCC |
| Explanations | Declaration of conformity Declaration of conformity UK |
