

Rittal – The System.

Faster – better – everywhere.



SV 9344.210

NH Fuse-Switch Disconnectors

State: 2026-05-26 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.210 - NH Fuse-Switch Disconnectors

Features

| | |
|--|---|
| Model No. | SV 9344.210 |
| Version | For mounting panel assembly. |
| Material | Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated |
| Color | Chassis: RAL 7035 Cover: RAL 7035/7001 |
| Clamping area for laminated copper bars: | Clamping area width: 50 mm Clamping area height: 10 mm |
| for mounting plate assembly | Yes |
| Cable outlet | Top/bottom |
| Type of connection (electrical) | Screw M10 |
| Rated operating current max. | 400 A |
| Rated operating voltage | 690 V, 3~ |
| For NH size | 2 |
| Note | The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses". |
| Test specification | IEC 60 947-3 IEC 60 269-2 (fuse inserts) |
| Dimensions | Width: 210 mm Height: 298 mm |
| Connection of round conductors | 10 - 240 mm ² |
| Number of poles | 3-pole |
| Round conductor cross-section | 10 - 240 mm ² |
| Packaging unit | 1 pc(s). |
| Net weight | 3.08 kg |

Features

| | |
|------------------------------|--|
| Gross weight | 3.098 kg |
| Copper weight (kg per piece) | 1 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC000249 |
| ECLASS 8.0 | 27371401 |
| Product description | SV NH fuse-switch disconnecter, size 2, 400 A, 690 V, 3-pole, screw M10, for mounting plate assembly |

Approvals

| | |
|--------------|---|
| Approvals | C-UR CQC-CCC UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |