

**Rittal – The System.**

Faster – better – everywhere.



**RX 9362.115**

**RiLineX NH fuse switch  
disconnector**

State: 2026-02-13 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# RX 9362.115 - RiLineX NH fuse switch disconnector

RiLineX NH fuse-switch-disconnector in size 1 for 60 mm busbar systems. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnectors have a park position to simplify maintenance work. Connection version with M10 screw connection. Cable outlet can be individually converted at the top or bottom. Including electronic fuse monitoring.



## Features

Model No.	RX 9362.115
Version	For 60 mm busbar systems
Benefits	<p>Cover, lockable and sealable</p> <p>Voltage test through separate opening</p> <p>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm</p> <p>Tool-free conversion of the cable outlet</p> <p>Park position for simplified maintenance work</p> <p>All variants also with electronic fuse monitoring</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire behavior corresponding to UL 94</p> <p>Contact tracks: Electrolytic copper, silver-plated</p>
Color	<p>RAL 9005</p> <p>RAL 35745</p>
Supply includes	Incl. connection plug for electrical fuse monitoring
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10

# Features

Rated current max.	250 A
Rated operating current max.	250 A
Rated operating voltage	690 V AC
For NH size	1
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 181.5 mm Height: 348.5 mm Depth: 116.7 mm
Operating temperature range	-5 °C...35 °C
Storage temperature range	-25 °C...70 °C
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Suitable for busbar system	RiLineX RiLine60
Number of poles	3-pole
Utilization category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) DC-22B (250 V/100 A) DC-21B (440 V/100 A)
Contamination level	3
With electronic fuse monitoring	Yes
Protection category IP to IEC 60 529	IP 2XB
Fire load	36.19 MJ/m <sup>2</sup>
Power dissipation (max.)	51 W
Packaging unit	1 pc(s).
Net weight	2.7
Gross weight	2.728

## Features

---

Copper weight (kg per piece)	0.8
Customs tariff number	85369095
ETIM 9	EC001040

## Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------