


# Rittal – The System.

Faster – better – everywhere.



## SV 9345.005 Fuse Holders

State: 2025-08-31 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9345.005 - Fuse Holders 31 A to 60 A

Fuse holder up to 60 A, 3-pole. Simple mounting on support rails or via OM component adapters.

## Features

|                                    |  |
|------------------------------------|--|
| Model No.                          | SV 9345.005  |
| Material                           | Polyamide<br>Fire protection corresponding to UL 94-V0   |
| Color                              | RAL 7035   |
| Connection for round conductor     | AWG 8 - 18   |
| For fuse type (class)              | CC   |
| Rated operating current max.       | 30 A   |
| Rated operating voltage            | 600 V, 3~  |
| Fuse standard                      | UL 248-4   |
| Note                               | For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adapter combinations (OM adapters/supports) |
| Test specification                 | UL 4248-1<br>UL 4248-4<br>UL 4248-8  |
| Note on Model No.:                 | Not suitable for 10 x 38 mm fuses as per IEC 60 269-2/-4/-6  |
| Dimensions                         | Width: 54 mm<br>Height: 81 mm  |
| Connection of round conductors     | 0.75 - 25 mm <sup>2</sup>  |
| Suitable for fuses                 | Diameter: 10 mm<br>Length: 38 mm   |
| Voltage range for indicator lights | 110 - 600 V  |
| Electrical UL ratings (SCCR)       | 200 kA - 600 V, fuse class CC max. 30 A, JDDZ/7  |
| Number of poles                    | 3-pole   |
| Packaging unit                     | 4 pc(s).   |

# Features

|                              |               |
|------------------------------|---------------|
| Net weight                   | 0.4           |
| Gross weight                 | 0.634         |
| Copper weight (kg per piece) | 0.018         |
| Customs tariff number        | 85369095      |
| EAN                          | 4028177805385 |
| ETIM 9                       | EC001644      |
| ECLASS 8.0                   | 27400613      |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |