

Rittal – The System.

Faster – better – everywhere.



SV 9345.600 Circuit-Breaker Component Adaptors

State: 2026-07-03 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.600 - Circuit-Breaker Component Adaptors 3-pole

Circuit breaker adaptor for the universal, simplified assembly of circuit-breakers.



Features

| | |
|---|--|
| Model No. | SV 9345.600 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| Supply includes | Connection straps Sliding Blocks |
| Rated current max. | 250 A |
| Rated operating voltage | 690 V, 3~ |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications. |
| Electrical UL ratings (SCCR) | 65 kA - 480 V, circuit breaker max. 250 A, DIVQ/7 |
| Cable outlet | Top |
| For bar systems with center-to-center spacing | 60 mm |
| Number of poles | 3-pole |
| Dimensions | Width: 105 mm Height: 240 mm |
| Suitable for busbars | Height: 5, 10 mm |

Features

| | |
|------------------------------|--|
| To fit manufacturer (model) | ABB (S3, T3, T4/320 A, T3 UL, T4 UL, XT3, XT4) Allen Bradley (140U-J) Eaton (NZM2, NZM2 UL, BZM B2) GE (FE160, FE250, FD160) Legrand (DPX 250) Mitsubishi (NF125-SGW/HGW, NF160-SGW/HGW) OEZ (BD250N, BD250S) Schneider Electric (NS(X)100, NS(X)160, NS(X)250, GV7, NSF150, NSF250) Schrack (MC2) Siemens (VL150(X) UL, VL160(X), VL250, VL250 UL, 3RV10 63, 3RV13 63, 3RV13 64, 3VT2, 3VA12/20/21/22, 3VA52/61/62) Terasaki (H125, L125, H160, L160, S160, E250, H250, L250) |
| Approvals | UL |
| Packaging unit | 1 pc(s). |
| Net weight | 1.426 kg |
| Gross weight | 1.509 kg |
| Copper weight (kg per piece) | 0.77 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Circuit-breaker component adaptor, 250 A, 690 V, 3-pole, cable outlet top, with connection straps |

Approvals

| | |
|-----------|---|
| Approvals | ABS DNV Lloyds Register UL + C-UL (listed) |
|-----------|---|

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|