Rittal - The System.

Faster – better – everywhere.






RX 9362.422 RiLineX NH fuse switch disconnector

State: 2025-11-03 (Source: rittal.com/ca-en)



RX 9362.422 - RiLineX NH fuse switch disconnector

RiLineX NH fuse-switch-disconnector in size 000 for 60 mm busbar systems. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnectors have a park position to simplify maintenance work. Connection design with box terminal for connecting round conductors min. 1.5 bis max. 50 mm². Cable outlet at top.



Features

| Model No. | RX 9362.422 |
|---------------------------------|--|
| Benefits | Cover, lockable and sealable |
| | Voltage test through separate opening |
| | Snap-on mounting up to 250 A and simple adjustment to busbar |
| | thickness 5/10 mm |
| | Tool-free conversion of the cable outlet |
| | Park position for simplified maintenance work |
| | All variants also with electronic fuse monitoring |
| Material | Polyamide (PA 6) |
| | Fire behavior corresponding to UL 94 |
| | Contact tracks: Electrolytic copper, silver-plated |
| Color | RAL 9005 |
| | RAL 35745 |
| For bar systems with center-to- | 60 mm |
| center spacing | |
| Cable outlet | Тор |
| Type of connection (electrical) | Box terminal |
| Rated insulation voltage | 1,000 V |
| Rated operating current max. | 125 A |
| | |

© Rittal 2025 2

Features

| Rated operating voltage | 690 V AC |
|--|--|
| For NH size | 000 |
| Test specification | IEC 60 947-3 IEC 60 269-2 (fuse inserts) |
| Dimensions | Width: 53 mm Height: 212 mm Depth: 103 mm |
| Operating temperature range | -5 °C35 °C |
| Storage temperature range | -25 °C70 °C |
| Suitable for busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Suitable for busbar system | RiLineX RiLine60 |
| Number of poles | 3-pole |
| Utilization category | AC-23B (400 V/100 A) AC-22B (500 V/100 A) DC-22B (250 V/100 A) |
| Contamination level | 3 |
| Protection category IP to IEC 60 529 | IP 2XB |
| Fire load | 10.84 MJ/m² |
| Connection of round conductors, fine wire without wire end ferrule | 1.5 - 16 mm² |
| Connection of round conductors, fine wire with wire end ferrule | 1.5 - 50 mm² |
| Power dissipation (max.) | 36 W |
| Packaging unit | 1 pc(s). |
| Net weight | 0.65 |
| Gross weight | 0.706 |
| Copper weight (kg per piece) | 0.475 |
| | |

© Rittal 2025 3

Features

| Customs tariff number | 85369095 |
|-----------------------|----------|
| ETIM 9 | EC001040 |

Approvals

Explanations Declaration of conformity

© Rittal 2025