

Rittal – The System.

Faster – better – everywhere.



RX 9363.005

RiLineX NH fuse switch disconnecter

State: 2026-04-04 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9363.005 - RiLineX NH fuse switch disconnecter

RiLineX NH fuse-switch-disconnector in sizes 00 for mounting plates. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnecters have a park position to simplify maintenance work. Connection version with M8 screw connection. Including electronic fuse monitoring.



Features

Model No.	RX 9363.005
Version	For mounting panel assembly.
Benefits	Cover, lockable and sealable Voltage test through separate opening Tool-free conversion of the cable outlet Park position for simplified maintenance work All variants also with electronic fuse monitoring
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	RAL 9005 RAL 35745
Supply includes	Incl. connection plug for electrical fuse monitoring
for mounting plate assembly	Yes
Cable outlet	Top/bottom

Features

Type of connection (electrical)	Screw M8
Fuse inserts	NH 00 NH 000
Rated insulation voltage U_i	1,000 kV
Rated operating voltage	690 V AC
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 228.9 mm Depth: 86.1 mm
Operating temperature range	-5 °C...35 °C
Storage temperature range	-25 °C...70 °C
Number of poles	3-pole
Utilization category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A)
Contamination level	3
With electronic fuse monitoring	Yes
Protection category IP to IEC 60 529	IP 2XB
Fire load	13.24 MJ/m ²
Power loss max.	16 W
Heat loss per fuse insert (max.)	12 W
Packaging unit	1 pc(s).
Net weight	0.82 kg
Gross weight	0.917 kg
Copper weight (kg per piece)	0.18
Customs tariff number	85369095

Features

ETIM 9	EC001040
Product description	RX NH fuse-switch-disconnector size 00, 160 A, 3-pole, M8 screw, with fuse monitoring 800 V, mounting plate assembly

Approvals

Explanations	Declaration of conformity PCF-declaration
--------------	--
